

NON-ABSORBABLE SUTURE

Monopractilon



Type

Monofilament

Composition

Extrusion of polyamide 6.0 or 6.6

Coating

None

Colour

Blue or Black

Tissue reaction

Minimal

Absorption

Non absorbable, gradually encapsulated by connective tissue. The thread mass diminishes, approximately 10% a year by rupture of chemical links (hydrolytic action).

Presentation

Box with 12 sutures





NON-ABSORBABLE SUTURE

Monopractilon



Characteristics

- High tensile strength, non absorbable
 - + Excellent and permanent tissue support
- Synthetic
 - + Minimal tissue reaction
- Monofilament with microscopic uniform diameter
 - + Soft passage through the tissues without sawing, tissue drag and trauma
 - + Absence of capillarity (no support of bacterial growth)
 - + Excellent knot tie down

- Pliability and softness
 - + Good handling properties
 - + Easy and secure knotting
- Hermetically sealed packing
 - + Guaranteed seal and product sterility

Indications

General soft tissue closing and/or ligation

MONOPRACTILON BLUE ESPECIALLY IN:

- + Skin closure
- + General surgery
- + Plastic surgery
- Gastrointestinal surgery
- + Gynaecology
- Obstetrics
- Orthopaedics

MONOPRACTILON BLACK ESPECIALLY IN:

- + Plastic surgery
- + Ophthalmic surgery

Tailored for surgery



NON-ABSORBABLE SUTURE

Monopractilon ()



Usp	Met.	Len.	Needle	Col.	Description	N.Type
11/0	0,1	30	DOUBLE	•	6 mm 3/8 150 MICR.	€
10/0	0,2	13	DOUBLE		4 mm 3/8 150 MICR	⇔
10/0	0,2	30	DOUBLE	•	4,75 mm 3/8 150 MICR.	≪>
10/0	0,2	30	DOUBLE	•	6 mm 3/8 220 MICR	W
10/0	0,2	45	DOUBLE		6 mm 3/8 150 MICR.	€
10/0	0,2	30	DOUBLE	•	6 mm 3/8 150 MICR.	⇔
10/0	0,2	13	SINGLE	•	6,35 mm 3/8 140 MICR.	0
9/0	0,3	13	SINGLE		4,75 mm 3/8 130 MICR.	0
8/0	0,4	13	SINGLE	•	6,5 mm 3/8 130 MICR	0
8/0	0,4	45	DOUBLE		8 mm 3/8 220 MICR.	0
8/0	0,4	45	SINGLE	•	8 mm 1/2 220 MICR.	€
7/0	0,5	45	SINGLE		8 mm 3/8 230 MICR.	000
6/0	0,7	45	SINGLE	•	8 mm 3/8 280 MICR.	0
6/0	0,7	45	SINGLE		10 mm 3/8 330 MICR	V
6/0	0,7	75	SINGLE	•	19 mm 3/8	∇
5/0	1	75	SINGLE		16 mm 3/8	A
5/0	1	45	SINGLE		19 mm 3/8	∇
5/0	1	45	SINGLE		19 mm 3/8	A
5/0	1	75	SINGLE		19 mm 3/8	∇
5/0	1	75	SINGLE		20 mm 1/2	0
4/0	1,5	45	SINGLE	•	12 mm 3/8 430 MICR	∇
4/0	1,5	75	SINGLE		16 mm 3/8	V
4/0	1,5	45	SINGLE		16 mm 3/8	∇
4/0	1,5	75	SINGLE		16 mm 3/8	V
4/0	1,5	45	SINGLE		19 mm 3/8	∇
4/0	1,5	75	SINGLE		19 mm 3/8	∇
4/0	1,5	75	SINGLE		19 mm 3/8	∇
4/0	1,5	75	SINGLE		19 mm 3/8	Δ
4/0	1,5	90	DOUBLE		20 mm 1/2	0
4/0	1,5	75	SINGLE		20 mm 1/2	0
4/0	1,5	75	SINGLE		24 mm 3/8	A
4/0	1,5	45	SINGLE		25 mm 3/8	V
4/0	1,5	75	SINGLE		25 mm 3/8	∇
4/0	1,5	75	SINGLE		30 mm 3/8	V
3/0	2	45	SINGLE		16 mm 1/2	0
3/0	2	45	SINGLE		18 mm 1/2	0
3/0	2	75	SINGLE		19 mm 3/8	\triangle
3/0	2	45	SINGLE	•	19 mm 3/8	V
3/0	2	75	SINGLE		19 mm 3/8	∇
3/0	2	45	SINGLE	•	20 mm 3/8	V
3/0	2	90	DOUBLE		20 mm 1/2	0
3/0	2	75	SINGLE		20 mm 1/2	0
3/0	2	75	SINGLE		24 mm 3/8	∇
3/0	2	45	SINGLE		26 mm 3/8	V
3/0	2	75	SINGLE		26 mm 3/8	∇
3/0	2	75	SINGLE		26 mm 1/2	0
3/0	2	45	SINGLE		26 mm 1/2	0
3/0	2	75	SINGLE		26 mm 3/8	V
3/0	2	75	SINGLE		35 mm 3/8	V
2/0	3	75	SINGLE		24 mm 3/8	V

Usp	Met.	Len.	Needle	Col.	Description	N.Type
2/0	3	75	SINGLE		25 mm 3/8	∇
2/0	3	45	SINGLE		26 mm 3/8	∇
2/0	3	75	SINGLE		26 mm 1/2	\odot
2/0	3	75	SINGLE		26 mm 3/8	∇
2/0	3	75	SINGLE		30 mm 1/2	\odot
2/0	3	45	SINGLE	•	30 mm 3/8	∇
2/0	3	75	SINGLE		30 mm 3/8	∇
2/0	3	75	SINGLE	•	30 mm 1/2	∇
2/0	3	75	SINGLE		35 mm 3/8	∇
2/0	3	75	SINGLE	•	35 mm 3/8	∇
2/0	3	45	SINGLE		40 mm 3/8	A
2/0	3	75	SINGLE		40 mm 3/8	∇
2/0	3	75	SINGLE	•	45 mm 3/8	∇
2/0	3	100	SINGLE		58 mm 3/8	∇
2/0	3	75	SINGLE		60 mm STRAIGHT	∇
0	3,5	75	SINGLE		26 mm 1/2	· O
0	3,5	75	SINGLE	•	30 mm 1/2	0
0	3,5	75	SINGLE		30 mm 1/2	∇
0	3,5	75	SINGLE		30 mm 3/8	∇
0	3,5	75	SINGLE		30 mm 3/8	∇
0	3,5	90	SINGLE		30 mm 1/2	\odot
0	3,5	45	SINGLE		35 mm 1/2	0
0	3,5	150	SINGLE		40 mm 1/2	0
0	3,5	100	SINGLE		40 mm 1/2	∇
0	3,5	150	SINGLE		50 mm 1/2 HEAVY LOOP	·
0	3,5	100	SINGLE		50 mm 1/2	0
0	3,5	150	SINGLE		50 mm 1/2 LDOP	0
0	3,5	150	SINGLE		50 mm 1/2 LOOP	0
0	3,5	100	SINGLE		90 mm 3/8	A
1	4	75	SINGLE		30 mm 1/2	0
1	4	75	SINGLE		30 mm 3/8	∇
1	4	90	SINGLE		30 mm 3/8	∇
1	4	150	SINGLE		35 mm 1/2 LOOP	·
1	4	75	SINGLE		40 mm 1/2	0
1	4	100	SINGLE		40 mm 1/2	0
1	4	100	SINGLE		40 mm 1/2 LOOP	0
1	4	75	SINGLE		40 mm 1/2	0
1	4	75	SINGLE		40 mm 3/8	♥
1	4	75	SINGLE		45 mm 3/8	∇
1	4	150	SINGLE		45 mm 1/2 toop	0
1	4	75	SINGLE		45 mm 1/2	8
1	4	75	SINGLE		48 mm 1/2	∇
1	4	150	SINGLE		50 mm 1/2 HEAVY LOOP	·
1	4	150	SINGLE		50 mm 1/2 LOOP	0
1	4	150	SINGLE		50 mm 1/2 LOOP	0
1	4	75	SINGLE		50 mm 3/8 2 SUTURE VINYL TURE	₩
1	4	100	SINGLE		90 mm 3/8	A
1	4	50	SINGLE		90 mm 3/8	A
2	5	100	SINGLE		90 mm 3/8	A
2	5	75	SINGLE		48 mm 1/2	V
		and the same of				10.5 × 11 × 12

Our product range is not limited with the list above. The list is just given for example.

